

P1-04TEPS Cut Sheet



Productivity1000 relay output module, 4-point, 24 VAC/VDC, (4) solid state relays, 4 isolated common(s), 1 point(s) per common, 1A/point @ 50 °C, 0.75A/point @ 60 °C. Requires P1-10RTB or P1-10RTB-1 removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P1-04TEPS>

Technical Specifications

Brand	Productivity1000
Item	Output module
I/O Module Type	Relay
Number of Output Points	4
Nominal Output Voltage	24 VAC/VDC
Relay Configuration	(4) solid state relays
Number of Isolated Commons	4
Jumper Selectable Isolation	No
Number of Points per Common	1
Load Current	1A/point @ 50 °C, 0.75A/point @ 60 °C
Fuse Type	User-supplied external fuse
For Use With	Productivity1000
Requires	P1-10RTB or P1-10RTB-1 removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v4.6 or later

Agency Approvals

EU REACH	View EU REACH document
----------	--

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/P1-04TEPS.pdf>
See store item page for other formats.