

P1-08TD-TTL Cut Sheet



Productivity1000 discrete output module, 8-point, 5 VDC, sourcing/TTL, 2 common(s), 4 point(s) per common, 20 mA/point. Requires P1-10RTB or P1-10RTB-1 removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P1-08TD-TTL>

Technical Specifications

Brand	Productivity1000
Item	Output module
I/O Module Type	Discrete
Number of Output Points	8
Nominal Output Voltage	5 VDC
Discrete Output Type	Sourcing/TTL
Number of Non-Isolated Output Commons	2
Number of Points per Common	4
Load Current	20 mA/point
Fuse Type	User-supplied external fuse
Requires	P1-10RTB or P1-10RTB-1 removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v4.1 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document