


# P1-08TRS Cut Sheet



Productivity1000 relay output module, 8-point, 6-24 VDC/6-120 VAC, (6) Form A, (2) Form C, 8 isolated common(s), 1 point(s) per common, 3A/point. Requires P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P1-08TRS>

## Technical Specifications

<b>Brand</b>	Productivity1000
<b>Item</b>	Output module
<b>I/O Module Type</b>	Relay
<b>Number of Output Points</b>	8
<b>Nominal Output Voltage</b>	6-24 VDC/6-120 VAC
<b>Relay Configuration</b>	(6) Form A (SPST) relays, (2) Form C (SPDT) relays
<b>Number of Isolated Commons</b>	8
<b>Jumper Selectable Isolation</b>	No
<b>Number of Points per Common</b>	1
<b>Load Current</b>	3A/point
<b>Fuse Type</b>	External fusing 8A max (user supplied)
<b>Requires</b>	P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables
<b>Programming Software</b>	Productivity Suite programming software v3.0 or later

## Agency Approvals

<b>UL Listed File #</b>	E139594
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>