


P1-12CDRS Cut Sheet



Productivity1000 discrete combo module, Input: 8-point, 24 VAC/VDC, sinking/sourcing, Output: 4-point, 6–30 VDC / 6–120 VAC, relay, (4) Form A (SPST) relays, 5A/point, 2A/point if used with ZIPLink cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P1-12CDRS>

Technical Specifications

Brand	Productivity1000
Item	Combo module
I/O Module Type	Discrete
Number of Input Points	8
Nominal Input Voltage	24 VAC/VDC
Discrete Input Type	Sinking/sourcing
Number of Non-Isolated Discrete Input Commons	2
Number of Points per Discrete Input Common	8
Number of Output Points	4
Nominal Output Voltage	6–30 VDC / 6–120 VAC

Discrete Output Type	Relay
Relay Configuration	(4) Form A (SPST) relays
Number of Isolated Discrete Output Commons	4
Number of Points per Discrete Output Common	1
Load Current	5A/point, 2A/point if used with ZIPLink cable
Fuse Type	External fusing 8A max (user supplied)
Requires	P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v4.6 or later

Agency Approvals

EU REACH	View EU REACH document
----------	----------------------------------------

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/P1-12CDRS.pdf>
See store item page for other formats.