


P11EDB-DULD Cut Sheet



Metrol limit switch, tool setter, high precision touch, 27 x 38 x 18mm, 5mm flat head, tungsten carbide, 16mm plunger, 1.5N contact force, N.C. contact(s), 9.8ft/3m cable length, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P11EDB-DULD>

Technical Specifications

Brand	Metrol
Item	Limit switch
Application	Tool setter
Switch Type	High precision touch
Housing Size	27 x 38 x 18mm
Head Type	5mm flat
Actuator Type	16mm plunger
Contact Force	1.5N
Contact Type	N.C.
Cable Length	9.8ft/3m

Connection	Pigtail
Conductor Size	19 AWG
Stroke	5mm
Repeatability	0.0005mm
Material	Stainless steel
IP Rating	IP67
Operating Temperature	0 to 80 deg C
Indicating Type	LED indication
Mounting	Upward
Mounting Hole Spacing	10mm

Agency Approvals

RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/P11EDB-DULD.pdf>
See store item page for other formats.