


P1AM-SERIAL Cut Sheet



ProductivityOpen serial shield, 2 ports, (2) RS-232/RS-485 (4-pin terminal) port(s). For use with ProductivityOpen P1AM-100 CPU.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P1AM-SERIAL>

Technical Specifications

Brand	ProductivityOpen
Item	Serial shield
Number of Ports	2
Communication Port and Connection Type(s)	(2) RS-232/RS-485 (4-pin terminal)
Port Protocol(s)	<ul style="list-style-type: none">• ASCII In/out• custom protocol(s)
Port Speed(s)	up to 115.2k baud
For Use With	ProductivityOpen P1AM-100 CPU
Programming Software	Arduino software (IDE) and ProductivityBlocks

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/P1AM-SERIAL.pdf>
See store item page for other formats.