

P2-16TD-TTL Cut Sheet



Productivity2000 discrete output module, 16-point, 5 VDC, sourcing/TTL, 2 common(s), 8 point(s) per common, 20 mA/point. Requires P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-16TD-TTL>

Technical Specifications

Brand	Productivity2000
Item	Output module
I/O Module Type	Discrete
Number of Output Points	16
Nominal Output Voltage	5 VDC
Discrete Output Type	Sourcing/TTL
Number of Non-Isolated Output Commons	2

Number of Points per Common	8
Load Current	20 mA/point
Fuse Type	User-supplied external fuse
Requires	P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v4.2 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/P2-16TD-TTL.pdf>
See store item page for other formats.