

P3-16DA-2 Cut Sheet



Productivity3000 analog output module, 16-channel, voltage, 16-bit, output voltage signal range(s) of +/- 10 VDC, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P3-16DA-2>

Technical Specifications

Brand	Productivity3000
Item	Output module
I/O Module Type	Analog
Number Of Output Channels	16
Output Signal Type	Voltage
Isolated Channels	No
Number of Non-Isolated Output Commons	2
Output Resolution	16-bit
Output Voltage Signal Range	+/- 10 VDC
Display Type	4 x 10 character LCD display
External Power Requirement	24 VDC
Requires	P3-RTB removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v1.2 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document