


P3-530 Cut Sheet



Productivity3000 CPU, up to 25 MB ladder memory, USB A storage, (1) Ethernet 10/100Base-T (RJ45), (1) RS-232 (RJ12), (1) RS-485 (3-pin terminal) and (1) USB A expansion port(s), battery included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P3-530>

Technical Specifications

Brand	Productivity3000
Item	CPU
Total Memory	Up to 25 MB
Ladder Memory	Up to 25 MB
User Data Memory	Up to 25 MB
Removable Media Type	USB A storage
Programming Language	Ladder
Programming Software	Productivity Suite programming software v1.7 or later
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (1) Ethernet 10/100Base-T (RJ45)• (1) RS-232 (RJ12)• (1) RS-485 (3-pin terminal)• (1) USB A expansion
Port Protocol(s)	<ul style="list-style-type: none">• MQTT Client• Modbus RTU Master/Slave• Modbus TCP• ASCII In/out• TCP/IP• UDP/IP• local expansion I/O• webserver (non-secure HTTP)• programming and monitoring

Port Speed(s)	<ul style="list-style-type: none">• 10/100 Mbps• up to 115.2k baud
Real Time Clock/Calendar	Yes
Retentive Memory	Yes
Battery Backup	Yes
Includes	D2-BAT-1 battery
Dangerous Goods	<ul style="list-style-type: none">• Battery Installed: No• Packaging Instructions: 969• UN Number: UN3091• Hazard Type: Lithium Batteries• Battery Type: Button• Lithium Content: 0.17• Replacement Battery: D2-BAT-1• Generic Battery: CR2354

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/P3-530.pdf>
See store item page for other formats.