

P3-622 Cut Sheet



Productivity3000 CPU, up to 50 MB ladder memory, 4 x 10 character LCD display, USB A storage, (2) Ethernet 10/100Base-T (RJ45), (1) RS-232/RS-485 (RJ12), (1) RS-232/RS-485 (4-pin terminal), (1) USB A expansion and (1) USB B port(s), battery included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P3-622>

Technical Specifications

Brand	Productivity3000
Item	CPU
Total Memory	Up to 50 MB
Ladder Memory	Up to 50 MB
User Data Memory	Up to 50 MB
Removable Media Type	USB A storage
Programming Language	Ladder
Programming Software	Productivity Suite programming software v4.4 or later
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (2) Ethernet 10/100Base-T (RJ45)• (1) RS-232/RS-485 (RJ12)• (1) RS-232/RS-485 (4-pin terminal)• (1) USB A expansion• (1) USB B
Port Protocol(s)	<ul style="list-style-type: none">• MQTT Client• MQTTs Client• Modbus RTU Master/Slave• Modbus TCP• ASCII In/out• TCP/IP• UDP/IP• EtherNet/IP explicit messaging scanner/adaptor• EtherNet/IP implicit messaging scanner/adaptor• Ethernet remote I/O• webserver (non-secure HTTP)• programming and monitoring
Port Speed(s)	<ul style="list-style-type: none">• 10/100 Mbps• up to 115.2k baud
Real Time Clock/Calendar	Yes
Retentive Memory	Yes
Battery Backup	Yes
Display Type	4 x 10 character LCD display
Includes	D2-BAT-1 battery

Dangerous Goods

- Battery Installed: No
- Packaging Instructions: 969
- UN Number: UN3091
- Hazard Type: Lithium Batteries
- Battery Type: Button
- Lithium Content: 0.17
- Replacement Battery: D2-BAT-1
- Generic Battery: CR2354

P3-622 Cut Sheet

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/P3-622.pdf>
See store item page for other formats.
