

P8-4906 Cut Sheet



Trumeter electromechanical counter, 4mm 6-digit analog, 24 VDC input, manual reset, rectangular 2-hole mount, (2) 10in 22 AWG pigtails.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P8-4906>

Technical Specifications

Brand	Trumeter
Item	Counter
Counter Type	Electromechanical
Count Direction	Up
Count Speed	600 counts/min
Display Type	Analog
Display Size	4mm 6-digit
Reset	Manual
Input	24 VDC
Operating Voltage	24 VDC
Mounting	Panel
Mounting Type	Rectangular 2-hole mount
Mounting Hole Size	2.00 x 1.01in
Connector Type	(2) 10in 22 AWG pigtails

Agency Approvals

UL Listed File #	None
UL Recognized File #	E36690
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document