

# P82F-3AT-PFA Cut Sheet



Norgren soft start valve, 3-port (3-way), 2-position, single solenoid spring return, N.C., 3/8in female NPT inlet(s), 3/8in female NPT outlet(s), 1/4in female NPT exhaust(s), Cv=1.8, 24 VDC operating voltage. For use with Excelon Plus 82 series components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P82F-3AT-PFA>

## Technical Specifications

<b>Brand</b>	Norgren
<b>Series</b>	Excelon Plus 82
<b>Item</b>	Valve
<b>Working Fluid</b>	Air
<b>Valve Type</b>	Soft start
<b>Action</b>	Single solenoid spring return
<b>Port Quantity</b>	3-port (3-way)
<b>Number Of Positions</b>	2
<b>Valve Configuration</b>	N.C.
<b>Inlet Port</b>	3/8in female NPT
<b>Outlet Port</b>	3/8in female NPT
<b>Exhaust Port</b>	1/4in female NPT
<b>Flow Coefficient</b>	1.8
<b>Operating Voltage</b>	24 VDC
<b>Electrical Connection</b>	8mm DIN style wiring plug
<b>For Use With</b>	Excelon Plus 82 series components
<b>Includes</b>	Field wireable DIN connector

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>