

# P84F-6AT-PFA Cut Sheet



Norgren soft start valve, 3-port (3-way), 2-position, single solenoid spring return, N.C., 3/4in female NPT inlet(s), 3/4in female NPT outlet(s), 1/2in female NPT exhaust(s), Cv=4, 24 VDC operating voltage. For use with Excelon Plus 84 series components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P84F-6AT-PFA>

## Technical Specifications

Brand	Norgren
Series	Excelon Plus 84
Item	Valve
Working Fluid	Air
Valve Type	Soft start
Action	Single solenoid spring return
Port Quantity	3-port (3-way)
Number Of Positions	2
Valve Configuration	N.C.

Inlet Port	3/4in female NPT
Outlet Port	3/4in female NPT
Exhaust Port	1/2in female NPT
Flow Coefficient	4
Operating Voltage	24 VDC
Electrical Connection	8mm DIN style wiring plug
For Use With	Excelon Plus 84 series components
Includes	Field wireable DIN connector

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/P84F-6AT-PFA.pdf>  
See store item page for other formats.