

PBGX6SSA Cut Sheet



Wiegmann pushbutton enclosure, 6 holes, 22mm, NEMA 4/4X/12/13, 9 x 5 x 4in (HxWxD), wall mount, 316 stainless steel, No. 3 intermediate polished finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PBGX6SSA>

Technical Specifications

| | |
|-------------------------------------|-----------------------------|
| Brand | Wiegmann |
| Item | Pushbutton enclosure |
| Number of Pushbutton Holes | 6 holes |
| Pushbutton Hole Nominal Size | 22mm |
| Slope Top | No |
| NEMA Rating | 4/4X/12/13 |
| Nominal Enclosure Dimensions | 9 x 5 x 4in (HxWxD) |
| Enclosure Height | 8.81in |
| Enclosure Width | 5.31in |
| Enclosure Depth | 4.58in |
| Mounting | Wall |
| Integral Mounting Feet | No |
| Integral Mounting Flange | Yes |
| Dual Access | No |
| Knockouts | No |
| Material | 316 stainless steel |
| Finish | No. 3 intermediate polished |
| Cover Type | Screw cover |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E64791 |
| UL Recognized File # | N/A |
| UL Hazardous File # | N/A |
| CE | None |
| CSA File # | N/A |
| RoHS Status | No |
| EU REACH | View EU REACH document |