


PBPA19008GY2 Cut Sheet



Hammond rack panel, 5U, 19in rack width, 5052-H32 aluminum, ANSI 61 gray, powder coat finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PBPA19008GY2>

Technical Specifications

| | |
|--------------------|-------------------|
| Brand | Hammond |
| Item | Rack panel |
| Rack Height | 5U |
| Rack Width | 19in |
| Height | 8.75in |
| Flanged | No |
| Knockouts | No |
| Perforated | No |
| Material | 5052-H32 aluminum |
| Color | ANSI 61 gray |
| Finish | Powder coat |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PBPA19008GY2.pdf>
See store item page for other formats.