

PE38-14-P Cut Sheet



HydroMode potable water push-to-connect fitting, plug-in elbow, acetal body, (1) 3/8in plug-in to (1) 1/4in tube connection(s), NSF/ANSI 61. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PE38-14-P>

Technical Specifications

| | |
|-------------------------------------|---|
| Brand | HydroMode |
| Item | Fitting |
| Working Fluid | Potable water |
| Fitting Connection Type | Push-to-connect |
| Fitting Type | Plug-in elbow |
| Body Material | Acetal |
| Connection | (1) 1/4in push-to-connect and (1) 3/8in plug-in |
| Operating Pressure | 145 psi |
| Operating Temperature | 32 to 158 deg F |
| Potable Water Certifications | NSF/ANSI 61 |
| Quantity per Pack | 5 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PE38-14-P.pdf>
See store item page for other formats.