

PGA070-25A1 Cut Sheet



SureGear high-precision planetary gearbox, 25:1 ratio, inline, 16mm diameter output shaft, nominal output torque 27 N-m (239 lb-in), 2-stage, 70mm frame. For use with SureServo and SureServo2 SV(2)L-201(B) motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PGA070-25A1>

Technical Specifications

| | |
|-------------------------------|---|
| Brand | SureGear |
| Item | Gearbox |
| Application | High-precision |
| Gearbox Type | Planetary |
| Gear Ratio | 25:1 |
| Output Configuration | Inline |
| Gearbox Output Shaft Diameter | 16mm |
| Nominal Output Torque | Nominal output torque 27 N-m (239 lb-in) |
| Number of Stages | 2 |
| Frame | 70mm |
| For Use With | SureServo and SureServo2 SV(2)L-201(B) motors |
| Includes | Motor mounting hardware and output shaft key |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PGA070-25A1.pdf>
See store item page for other formats.