

# PGB120-10A5 Cut Sheet



SureGear high-precision planetary gearbox, 10:1 ratio, right angle, 32mm diameter output shaft, nominal output torque 110 N-m (974 lb-in), 2-stage, 120mm frame. For use with SureServo and SureServo2 SV(2)M-210(B) motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PGB120-10A5>

## Technical Specifications

Brand	SureGear
Item	Gearbox
Application	High-precision
Gearbox Type	Planetary
Gear Ratio	10:1
Output Configuration	Right angle
Gearbox Output Shaft Diameter	32mm
Nominal Output Torque	Nominal output torque 110 N-m (974 lb-in)
Number of Stages	2
Frame	120mm
For Use With	SureServo and SureServo2 SV(2)M-210(B) motors
Includes	Input adapter bushing, motor mounting hardware and output shaft key

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/PGB120-10A5.pdf>  
See store item page for other formats.