

PGCN34-0550 Cut Sheet



SureGear precision planetary gearbox, 5:1 ratio, inline, 0.5in diameter output shaft, nominal output torque 26 N-m (230 lb-in), 1-stage, NEMA 34 frame. For use with SureStep NEMA 34 motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PGCN34-0550>

Technical Specifications

Brand	SureGear
Item	Gearbox
Application	Precision
Gearbox Type	Planetary
Gear Ratio	5:1
Output Configuration	Inline
Gearbox Output Shaft Diameter	0.5in
Nominal Output Torque	Nominal output torque 26 N-m (230 lb-in)
Number of Stages	1
Frame	NEMA 34
For Use With	SureStep NEMA 34 motors
Includes	Input adapter bushing for 1/2in motor shaft, motor mounting hardware and output shaft key

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document