

# PH100MLI Cut Sheet



Hammond control transformer, encapsulated core, 100 VA, 1-phase, 240/480 VAC primary, 25/120 VAC secondary, 50/60 Hz, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PH100MLI>

## Technical Specifications

|                      |                |
|----------------------|----------------|
| Brand                | Hammond        |
| Series               | Imperator      |
| Item                 | Transformer    |
| Transformer Type     | Control        |
| Core Type            | Encapsulated   |
| Power Rating         | 100 VA         |
| Number of Phases     | 1              |
| Primary Voltage      | 240/480 VAC    |
| Secondary Voltage    | 25/120 VAC     |
| Frequency            | 50/60 Hz       |
| Fused                | No             |
| Electrostatic Shield | No             |
| Mounting             | Panel          |
| Connection           | Screw terminal |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | E50394                                 |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | 003902                                 |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/PH100MLI.pdf>  
See store item page for other formats.