


PK-M-1000-L Cut Sheet



Gefran potentiometer linear position sensor, rodless slide, 1000mm stroke, 57 x 38 x 1167mm body, channel mount, 18mm DIN 43650 Form A.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PK-M-1000-L>

Technical Specifications

| | |
|--------------------------|------------------------|
| Brand | Gefran |
| Item | Linear position sensor |
| Transducer Type | Potentiometer |
| Action | Rodless slide |
| Stroke | 1000mm |
| Resistance | 10k ohm |
| Head Type | M5 |
| Head Material | Stainless steel |
| Housing Material | Anodized aluminum |
| Housing Size | 57 x 38 x 1167mm body |
| Sensor Resolution | Infinite |
| Linearity | +/- 0.05% |
| Switching Cycles | 25,000,000 cycles |
| Mounting | Channel |
| IP Rating | IP40 |
| Connection | 18mm DIN 43650 Form A |
| Number of Wires | 4 |
| Includes | Mounting hardware |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |
| Other | None |