


PMRU-2C-500A Cut Sheet



ProSense phase monitor relay, 3-phase, 35mm DIN rail mount, finger-safe, 190-500 VAC input voltage, DPDT, 10A contact rating, screw terminal(s), LED indicator(s), phase reversal, phase loss, phase unbalance, overvoltage and undervoltage protection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PMRU-2C-500A>

Technical Specifications

Brand	ProSense
Item	Relay
Relay Type	Phase monitor
Number of Phases	3
Mounting	35mm DIN rail
Relay Housing Type	Finger-safe
Input Voltage	190-500 VAC
Relay Configuration	DPDT
Connector Type	Screw terminal(s)
Contact Rating	10A
Indicator	LED
Protection Type(s)	<ul style="list-style-type: none">• phase reversal• phase loss• phase unbalance• overvoltage• undervoltage

Agency Approvals

UL Listed File #	E191059
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document