


PMW2-AP-3H Cut Sheet



ProSense inductive proximity sensor, tubular, 12mm diameter x 45mm body, stainless steel housing, PNP, N.O. output, 4mm sensing distance, flush, 100 Hz switching frequency, IP65 IP66 IP67 IP68 IP69K, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PMW2-AP-3H>

Technical Specifications

Brand	ProSense
Item	Proximity sensor
Sensor Type	Inductive
Application	Harsh duty and full metal
Shape	Tubular
Housing Size	12mm diameter x 45mm body
Housing Material	Stainless steel
Barrel Type	Threaded
Sensing Method	Extended sensing
Adjustable	No
Number of Wires	3
Switching Output	PNP

Operation Mode	N.O. output
Sensing Distance	4mm
Mounting Type	Flush
IO-Link Compatible	No
Switching Frequency	100 Hz
Operating Voltage	10-30 VDC
Operating Temperature	-25 to 70c
Weld Field Immune	No
Chip Immune	No
IP Rating	IP65 IP66 IP67 IP68 IP69K
Connection	4-pin M12 quick-disconnect
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PMW2-AP-3H.pdf>
See store item page for other formats.