

POC-CDR-M12 Cut Sheet



PocketCodr programming tool, 24 VDC output. USB-A to USB-C cable and 4-pin M12 male to female cable, 30 day trial activation of Contrinex Suite Plan CTXSUITE included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/POC-CDR-M12>

Technical Specifications

Brand	PocketCodr
Item	Programming tool
Output Voltage Range	24 VDC
Load Current	100 mA
Output Power	2.4 W
Includes	USB-A to USB-C cable and 4-pin M12 male to female cable, 30 day trial activation of Contrinex Suite Plan CTXSUITE

Dangerous Goods

- Battery Installed: YES
- Packaging Instructions: 966
- UN Number: UN3481
- Hazard Type: Lithium Polymer Battery
- Battery Type: Battery
- Watt Hours: 4.8
- Replacement Battery: N/A
- Generic Battery: N/A

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/POC-CDR-M12.pdf>
See store item page for other formats.