

# PS116Z11-LR200S200 Cut Sheet



Schmersal compact limit switch, plastic plunger, 45-degree adjustable head, (1) N.O./ (1) N.C. contact(s), snap action, 31mm wide body, 20-22mm hole spacing, die-cast zinc with plastic base, pigtail, 6.5ft/2m cable length, right exit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PS116Z11-LR200S200>

## Technical Specifications

<b>Brand</b>	Schmersal
<b>Item</b>	Limit switch
<b>Switch Type</b>	Compact
<b>Actuator Type</b>	Plastic plunger
<b>Head Type</b>	45-degree adjustable
<b>Contact Type</b>	(1) N.O./ (1) N.C.
<b>Action</b>	Snap action
<b>Reset</b>	No
<b>Body Width</b>	31mm

<b>Mounting Hole Spacing</b>	20-22mm
<b>Material</b>	Die-cast zinc with plastic base
<b>IP Rating</b>	IP66 IP67
<b>Operating Temperature</b>	-30 to 80 deg C
<b>Connection</b>	Pigtail
<b>Conductor Size</b>	0.50mm <sup>2</sup> (20 AWG)
<b>Cable Length</b>	6.5ft/2m
<b>Cable Exit</b>	Right

## Agency Approvals

<b>UL Listed File #</b>	E57648
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/PS116Z11-LR200S200.pdf>  
See store item page for other formats.