

PSD25-0P-1450H Cut Sheet



ProSense electronic pressure switch, 75 to 1450 psi set point, 316 stainless steel sensing element, PNP, N.O./N.C. complementary, 1/4in male NPT process connection, 9.6-32 VDC operating voltage, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSD25-0P-1450H>

Technical Specifications

Brand	ProSense
Item	Electronic pressure switch
Setpoint Range	75 to 1450 psi
Sensing Element Material	316 stainless steel
Switching Output	PNP, N.O./N.C. complementary
Process Connection	1/4in male NPT
Operating Voltage	9.6-32 VDC
IP Rating	IP67
Electrical Connection	4-pin M12 quick-disconnect
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E320431
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PSD25-0P-1450H.pdf>
See store item page for other formats.