

PSL-05-010 Cut Sheet



RHINO PSL series switching power supply, 5 VDC @ 1.5A/7.5W, 120/240 VAC or 125-375 VDC nominal input, 1-phase, enclosed, plastic housing, 35mm DIN rail mount, screw terminals, NEC Class 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSL-05-010>

Technical Specifications

| | |
|--------------------------------|---|
| Brand | RHINO |
| Item | Power supply |
| Series | PSL |
| Power Supply Type | Switching |
| Efficiency | 81% @115 VAC, 82% @230 VAC |
| Output Configuration | Single output |
| Output | 5 VDC @ 1.5A/7.5W |
| Output Voltage Range | 5 VDC |
| Input voltage range | 90-264 VAC/125-375 VDC |
| Number of Input Phases | 1 |
| Protection Type(s) | <ul style="list-style-type: none">• overvoltage• overcurrent• short circuit |
| Remote On/Off | No |
| Voltage Monitoring | Yes |
| Enclosure Type | Enclosed |
| Housing Material | Plastic |
| IP Rating | IP20 |
| Mounting | 35mm DIN rail |
| Connector Type | Screw terminals |
| NEC Class 2 | Yes |
| Integrated UPS Battery Control | No |
| Operating Temperature | -25 to 71 deg C |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E197592 |
| UL Recognized File # | E198298 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |