

# PSM24-BCM360S Cut Sheet



RHINO battery control module, 1 input, 24 VDC nominal input, 24-28 VDC output, 15A, alarm contact for operation monitoring, removable screw terminals. Requires PSM24 power supply, 24V battery (user-supplied).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSM24-BCM360S>

## Technical Specifications

Brand	RHINO
Item	Battery control module
Number of Inputs	1
Nominal Input Voltage	24 VDC
Input voltage range	24 VDC
Nominal Output Voltage	24 VDC
Output Voltage Range	24-28 VDC
Amperage Rating	15A
Protection Type(s)	<ul style="list-style-type: none"><li>• overvoltage</li><li>• overcurrent</li><li>• battery overcharge</li><li>• reverse polarity</li></ul>

Indicating Type	Single color LED for status indication and (3) output signals
Alarm Contact for Operation Monitoring	Yes
Remote On/Off	Yes
Housing Material	Metal
Mounting	35mm DIN rail
Connector Type	Removable screw terminals
Includes	(1) PSM-JC01 link cable and (1) PSM-TS temperature sensor
Requires	PSM24 power supply, 24V battery (user-supplied)

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/PSM24-BCM360S.pdf>  
See store item page for other formats.