

PSM24-REM360S Cut Sheet



RHINO redundancy module, 2 inputs, 24 VDC nominal input, 24-27 VDC output, 15A, alarm contact for operation monitoring, active current sharing, removable screw terminals. Requires (2) PSM24 power supplies.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSM24-REM360S>

Technical Specifications

Brand	RHINO
Item	Redundancy module
Number of Inputs	2
Nominal Input Voltage	24 VDC
Input voltage range	24-28 VDC
Nominal Output Voltage	24 VDC
Output Voltage Range	24-27 VDC
Amperage Rating	15A
Alarm Contact for Operation Monitoring	Yes
Active Current Sharing	Yes
Housing Material	Metal
Mounting	35mm DIN rail
Connector Type	Removable screw terminals
Requires	(2) PSM24 power supplies

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document