

# R149-040-000 Cut Sheet



Hammond suspension arm fitting, 90-degree swivel elbow, 300 degrees movement range, aluminum, RAL 7040 window gray, powder coat finish. For use with 60 x 40mm and 70mm taraPLUS suspension arm profiles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/R149-040-000>

## Technical Specifications

<b>Brand</b>	Hammond
<b>Item</b>	Suspension arm fitting
<b>Fitting Type</b>	90-degree swivel elbow
<b>Movement Range</b>	300 degrees
<b>Material</b>	Aluminum
<b>Color</b>	RAL 7040 window gray
<b>Finish</b>	Powder coat
<b>For Use With</b>	60 x 40mm and 70mm taraPLUS suspension arm profiles

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/R149-040-000.pdf>  
See store item page for other formats.