

RES10F06 Cut Sheet



Roxburgh EMI input filter, 120/240 VAC, 1-phase, 6A, panel mount, EMI/RFI filtering, 1-stage, general purpose, standard performance, 1/4in quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RES10F06>

Technical Specifications

Brand	Roxburgh
Item	Input filter
Filter Type	EMI
Filter Voltage Rating	120/240 VAC
Number of Input Phases	1
Amperage Rating	6A
On/Off Switch	No
Fused	No

Mounting	Panel
Filtering	EMI/RFI
Number of Filter Stages	1
SCCR Rating	5kA SCCR
Filter Application	General purpose
Filter Performance Level	Standard performance
Connector Type	1/4in quick-disconnect

Agency Approvals

UL Listed File #	None
UL Recognized File #	E191581
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/RES10F06.pdf>
See store item page for other formats.