

RIR-0622-H Cut Sheet



Roxburgh IEC inlet filter, 120/240 VAC, 1-phase, 6A, fused, screw mount, EMI/RFI filtering, 1-stage, general purpose, standard performance, 1/4in quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RIR-0622-H>

Technical Specifications

Brand	Roxburgh
Item	Inlet filter
Filter Type	IEC
Filter Voltage Rating	120/240 VAC
Number of Input Phases	1
Amperage Rating	6A
On/Off Switch	No
Fused	Yes

Mounting	Screw
Filtering	EMI/RFI
Number of Filter Stages	1
SCCR Rating	5kA SCCR
Filter Application	General purpose
Filter Performance Level	Standard performance
Connector Type	1/4in quick-disconnect

Agency Approvals

UL Listed File #	None
UL Recognized File #	E191581
UL Hazardous File #	None
CE	View CE declarations
CSA File #	207414
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/RIR-0622-H.pdf>
See store item page for other formats.