

RJ806HPL Cut Sheet



Stahlin RJ series enclosure, NEMA 1/3R/4X/6P/12, 8 x 6 x 6in (HxWxD), wall mount, fiberglass reinforced polyester, gray, raised single-door, (1) quick-release latch, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RJ806HPL>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Stahlin |
| Item | Enclosure |
| Series | RJ |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| NEMA Rating | 1/3R/4X/6P/12 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 8 x 6 x 6in (HxWxD) |
| Enclosure Height | 9.63in |
| Enclosure Width | 7.52in |
| Enclosure Depth | 6.20in |
| Mounting | Wall |
| Integral Mounting Feet | No |

| | |
|----------------------------------|---------------------------------|
| Integral Mounting Flange | Yes |
| Dual Access | No |
| Knockouts | No |
| Material | Fiberglass reinforced polyester |
| Color | Gray |
| Cover Type | Raised single-door |
| Hinge Type | Continuous hinge |
| Number of Hinges Per Door | 1 |
| Latch Type | (1) quick-release latch |
| Padlock Attachment Type | Padlock hasp and staple |
| Padlockable | Yes |
| Keylocking | No |

Agency Approvals

| | | |
|-----------------------------|--|---------|
| UL Listed File # | E64358 | E362920 |
| UL Recognized File # | E333478 | |
| UL Hazardous File # | None | |
| CE | View CE declarations | |
| CSA File # | LR069014 | |
| RoHS Status | Yes (See CE Doc) | |
| EU REACH | View EU REACH document | |