

RL9854AC45-135V Cut Sheet



Dold voltage monitor relay, 1-phase, 35mm DIN rail mount, 45-135 VAC input voltage, SPDT, 5A contact rating, screw terminal(s), LED indicator(s), overvoltage, undervoltage and voltage range protection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RL9854AC45-135V>

Technical Specifications

Brand	Dold
Item	Relay
Relay Type	Voltage monitor
Number of Phases	1
Mounting	35mm DIN rail
Relay Housing Type	Finger-safe
Input Voltage	45-135 VAC
Relay Configuration	SPDT
Connector Type	Screw terminal(s)
Contact Rating	5A
Indicator	LED
Protection Type(s)	<ul style="list-style-type: none">• overvoltage• undervoltage• voltage range

Agency Approvals

UL Listed File #	E107778
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/RL9854AC45-135V.pdf>
See store item page for other formats.