

RM1U1908SBK Cut Sheet



Hammond enclosure, 1U, 2 x 17 x 8in (HxWxD), rack or desktop mount, aluminum, black, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RM1U1908SBK>

Technical Specifications

| | |
|-------------------------------------|----------------------|
| Brand | Hammond |
| Item | Enclosure |
| Slope Top | No |
| 3-Piece Assembly | No |
| Vented | No |
| Nominal Enclosure Dimensions | 2 x 17 x 8in (HxWxD) |
| Enclosure Height | 1.75in |
| Enclosure Width | 16.60in |
| Enclosure Depth | 8.00in |
| Rack Height | 1U |
| Rack Width | 19in |
| Mounting | Rack or desktop |
| Integral Mounting Feet | No |

| | |
|---------------------------------|---|
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Bottom Gland Plate | No |
| Material | Aluminum |
| Color | Black |
| Finish | Powder coat |
| Cover Type | Screw cover |
| Shelf | No |
| Padlockable | No |
| Keylocking | No |
| Includes | (4) self-adhesive rubber feet, (2) mounting brackets, and mounting hardware |
| Additional Information | Assembly required |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/RM1U1908SBK.pdf>
See store item page for other formats.