

RM1U1928VBK Cut Sheet

Hammond enclosure, 1U, vented, 2 x 17 x 28in (HxWxD), rack or desktop mount, aluminum, black, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RM1U1928VBK>

Technical Specifications

Brand	Hammond
Item	Enclosure
Slope Top	No
3-Piece Assembly	No
Vented	Yes
Nominal Enclosure Dimensions	2 x 17 x 28in (HxWxD)
Enclosure Height	1.75in
Enclosure Width	16.60in
Enclosure Depth	28.00in
Rack Height	1U
Rack Width	19in
Mounting	Rack or desktop
Integral Mounting Feet	No

Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	Aluminum
Color	Black
Finish	Powder coat
Cover Type	Screw cover
Shelf	No
Padlockable	No
Keylocking	No
Includes	(4) self-adhesive rubber feet, (2) mounting brackets, and mounting hardware
Additional Information	Assembly required

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/RM1U1928VBK.pdf>
See store item page for other formats.