

RM25030-1SR Cut Sheet



Bussmann modular fuse block, accepts R fuses, 30A, 250V, 1-pole, 18-10 AWG copper only, screw with pressure plate, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RM25030-1SR>

Technical Specifications

Brand	Bussmann
Item	Fuse block
Modular	Yes
Blown Fuse Indicator	No
Multi-Wire	No
Accepts Fuse Class	R
Amperage Rating	30A
Voltage Rating	250V
Number of Poles	1
Conductor Size	18-10 AWG copper only
Conductor Connection Type	Screw with pressure plate
SCCR Rating	200kA SCCR
Fuse Connection Type	Clip with reinforced spring
Mounting	35mm DIN rail or panel
Additional Information	Covers sold separately

Agency Approvals

UL Listed File #	E14853
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	47235-6225-01
RoHS Status	No
EU REACH	View EU REACH document
Other	None