

# RM3U1908VBK Cut Sheet



Hammond enclosure, 3U, vented, 5 x 17 x 8in (HxWxD), rack or desktop mount, aluminum, black, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RM3U1908VBK>

## Technical Specifications

|                                     |                      |
|-------------------------------------|----------------------|
| <b>Brand</b>                        | Hammond              |
| <b>Item</b>                         | Enclosure            |
| <b>Slope Top</b>                    | No                   |
| <b>3-Piece Assembly</b>             | No                   |
| <b>Vented</b>                       | Yes                  |
| <b>Nominal Enclosure Dimensions</b> | 5 x 17 x 8in (HxWxD) |
| <b>Enclosure Height</b>             | 5.25in               |
| <b>Enclosure Width</b>              | 16.60in              |
| <b>Enclosure Depth</b>              | 8.00in               |
| <b>Rack Height</b>                  | 3U                   |
| <b>Rack Width</b>                   | 19in                 |
| <b>Mounting</b>                     | Rack or desktop      |
| <b>Integral Mounting Feet</b>       | No                   |

|                                 |   |
|---------------------------------|---|
| <b>Integral Mounting Flange</b> | No  |
| <b>Dual Access</b>              | No  |
| <b>Knockouts</b>                | No  |
| <b>Bottom Gland Plate</b>       | No  |
| <b>Material</b>                 | Aluminum  |
| <b>Color</b>                    | Black   |
| <b>Finish</b>                   | Powder coat   |
| <b>Cover Type</b>               | Screw cover   |
| <b>Shelf</b>                    | No  |
| <b>Padlockable</b>              | No  |
| <b>Keylocking</b>               | No  |
| <b>Includes</b>                 | (4) self-adhesive rubber feet, (2) mounting brackets, and mounting hardware |
| <b>Additional Information</b>   | Assembly required   |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | None  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/RM3U1908VBK.pdf>  
See store item page for other formats.