

# RM4U1908SBK Cut Sheet



Hammond enclosure, 4U, 7 x 17 x 8in (HxWxD), rack or desktop mount, aluminum, black, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RM4U1908SBK>

## Technical Specifications

<b>Brand</b>	Hammond
<b>Item</b>	Enclosure
<b>Slope Top</b>	No
<b>3-Piece Assembly</b>	No
<b>Vented</b>	No
<b>Nominal Enclosure Dimensions</b>	7 x 17 x 8in (HxWxD)
<b>Enclosure Height</b>	7.00in
<b>Enclosure Width</b>	16.60in
<b>Enclosure Depth</b>	8.00in
<b>Rack Height</b>	4U
<b>Rack Width</b>	19in
<b>Mounting</b>	Rack or desktop
<b>Integral Mounting Feet</b>	No

<b>Integral Mounting Flange</b>	No
<b>Dual Access</b>	No
<b>Knockouts</b>	No
<b>Bottom Gland Plate</b>	No
<b>Material</b>	Aluminum
<b>Color</b>	Black
<b>Finish</b>	Powder coat
<b>Cover Type</b>	Screw cover
<b>Shelf</b>	No
<b>Padlockable</b>	No
<b>Keylocking</b>	No
<b>Includes</b>	(4) self-adhesive rubber feet, (2) mounting brackets, and mounting hardware
<b>Additional Information</b>	Assembly required

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/RM4U1908SBK.pdf>  
See store item page for other formats.