


RTH-D16RA-NF0-901 Cut Sheet



Contrinex basic RFID tag, round, 16mm diameter, non-flush mount, HF communication, 13.56 MHz, EEPROM memory, 320 bytes, IP67. Package of 10.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RTH-D16RA-NF0-901>

Technical Specifications

Brand	Contrinex
Item	RFID tag
Tag Type	Basic
Shape	Round
Size	16mm diameter
Mounting	Non-flush
Communication Type	HF
RFID Frequency	13.56 MHz

Memory Type	EEPROM
Total Memory	320 bytes
User Memory	160 bytes
Material	Polyphenylene sulfide and epoxy
IP Rating	IP67
Operating Temperature	-20 degrees to 85 degrees C
Quantity per Pack	10

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/RTH-D16RA-NF0-901.pdf>
See store item page for other formats.