


# RWB40E-3-R4U025 Cut Sheet



WEG Electric RWB40E series electronic overload relay, 5–25.0A adjustable, solid state, remote/local reset, direct mount power connection(s). For use with CWB9 to CWB38 and CWBN00 to CWBN1series contactors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RWB40E-3-R4U025>

## Technical Specifications

Brand	WEG Electric
Item	Relay
Series	RWB40E
Relay Type	Electronic overload
Full Load Amperage Range	5–25.0A adjustable
Operation Type	Solid state
Auxiliary Contacts	(1) N.O. / (1) N.C.
Trip Class	Trip Class 10/20/30

Reset	Remote/local
Phase Loss Sensitive	Yes
Ground Fault Protection	No
Connection	Direct mount power
For Use With	CWB9 to CWB38 and CWBN00 to CWBN1series contactors
Additional Information	Self powered

## Agency Approvals

UL Listed File #	E189202
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/RWB40E-3-R4U025.pdf>  
See store item page for other formats.