

S-3B-TRX Cut Sheet



ReeR safety light curtain, active/passive pair, body protection, 24 VDC, 400mm resolution, 810mm protected height, 0-8m operating distance, safety category Type 4, IP65 IP67, (1) 8-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/S-3B-TRX>

Technical Specifications

Brand	ReeR
Series	Safegate
Item	Safety light curtain
Light Curtain Type	Active/passive pair
Function	Body protection
Input Voltage	24 VDC
Beam Resolution	400mm
Protected Height	810mm
Operating Distance	0-8m

Safety Category	Type 4
Switching Output	(2) OSSD outputs
Connection	(1) 8-pin M12 quick-disconnect
IP Rating	IP65 IP67
Configurable	No
Light Curtain Features	External device monitoring and restart capability
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E193188
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/S-3B-TRX.pdf>
See store item page for other formats.