

SB114-061-G-M Cut Sheet



Comepi control station, polycarbonate, (1) key switch, key-operated, 2-position, black, maintained, (1) N.O. contact(s). Requires 5-pin female M12 cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SB114-061-G-M>

Technical Specifications

Brand	Comepi
Series	SB
Item	Control station
Factory Sealed	No
Housing Material	Fiberglass-reinforced polycarbonate
Control Station Configuration	(1) key switch
Number Of Positions	2
Key Removable Position	Key removable left position

Operator Type	Key-operated
Operator Size	30mm
Operator Color	Black
Action	Maintained
Contact Type	(1) N.O.
IP Rating	IP65
Requires	5-pin female M12 cable

Agency Approvals

UL Listed File #	E189258
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SB114-061-G-M.pdf>
See store item page for other formats.