

SB214-024-G-M Cut Sheet



Comepi control station, polycarbonate, (2) pushbuttons, multi-operator, red/green, momentary, (1) N.O. and (1) N.C. contact(s), operator text (I) and (O). Requires 5-pin female M12 cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SB214-024-G-M>

Technical Specifications

Brand	Comepi
Series	SB
Item	Control station
Factory Sealed	No
Housing Material	Fiberglass-reinforced polycarbonate
Control Station Configuration	(2) pushbuttons
Operator Type	Flush/flush

Operator Size	30mm/30mm
Operator Color	Red/green
Operator Legend	(I) and (O)
Action	Momentary
Contact Type	(1) N.O. and (1) N.C.
IP Rating	IP65
Requires	5-pin female M12 cable

Agency Approvals

UL Listed File #	E189258
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SB214-024-G-M.pdf>
See store item page for other formats.