

SB314-017-G-M Cut Sheet



Comepi control station, polycarbonate, (3) pushbuttons, multi-operator, green/red/green, momentary, (1) N.O., (1) N.C. and (1) N.O. contact(s), operator text (I), (O) and (II). Requires 8-pin female M12 cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SB314-017-G-M>

Technical Specifications

Brand	Comepi	Operator Size	30mm/30mm/30mm
Series	SB	Operator Color	Green/red/green
Item	Control station	Operator Legend	(I), (O) and (II)
Factory Sealed	No	Action	Momentary
Housing Material	Fiberglass-reinforced polycarbonate	Contact Type	(1) N.O., (1) N.C. and (1) N.O.
Control Station Configuration	(3) pushbuttons	IP Rating	IP65
Operator Type	Flush/extended/flush	Requires	8-pin female M12 cable

Agency Approvals

UL Listed File #	E189258
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SB314-017-G-M.pdf>
See store item page for other formats.