

SB414-01B-G-M Cut Sheet



Comepi control station, polycarbonate, (4) pushbuttons, multi-operator, red/white/black/blue, twist-to-release/momentary, (1) N.C., (1) N.O., (1) N.O. and (1) N.O. contact(s), operator text arrow, up arrow, down arrow and RESET. Requires 8-pin female M12 cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SB414-01B-G-M>

Technical Specifications

Brand	Comepi	Operator Size	40mm/30mm/30mm/30mm
Series	SB	Operator Color	Red/white/black/blue
Item	Control station	Operator Legend	Arrow, up arrow, down arrow and RESET
Factory Sealed	No	Action	Twist-to-release/momentary
Housing Material	Fiberglass-reinforced polycarbonate	Contact Type	(1) N.C., (1) N.O., (1) N.O. and (1) N.O.
Control Station Configuration	(4) pushbuttons	IP Rating	IP65
Operator Type	Mushroom/flush/flush/flush	Requires	8-pin female M12 cable

Agency Approvals

UL Listed File #	E189258
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SB414-01B-G-M.pdf>
See store item page for other formats.