


SC060606G Cut Sheet



Wiegmann enclosure, NEMA 1, 6 x 6 x 6in (HxWxD), wall mount, with knockouts, galvanized steel, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC060606G>

Technical Specifications

Brand	Wiegmann	Integral Mounting Feet	No
Item	Enclosure	Integral Mounting Flange	No
Slope Top	No	Dual Access	No
NEMA Rating	1	Knockouts	Yes
Nominal Enclosure Height	6in	Material	Galvanized steel
Nominal Enclosure Width	6in	Cover Type	Screw cover
Nominal Enclosure Depth	6in	Padlockable	No
Mounting	Wall	Keylocking	No

Agency Approvals

UL Listed File #	E23553
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SC060606G.pdf>
See store item page for other formats.