

# SC121810G Cut Sheet



Wiegmann enclosure, NEMA 1, 18 x 12 x 10in (HxWxD), wall mount, with knockouts, galvanized steel, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC121810G>

## Technical Specifications

|                                 |           |
|---------------------------------|-----------|
| <b>Brand</b>                    | Wiegmann  |
| <b>Item</b>                     | Enclosure |
| <b>Slope Top</b>                | No        |
| <b>NEMA Rating</b>              | 1         |
| <b>Nominal Enclosure Height</b> | 18in      |
| <b>Nominal Enclosure Width</b>  | 12in      |
| <b>Nominal Enclosure Depth</b>  | 10in      |
| <b>Mounting</b>                 | Wall      |

|                                 |                  |
|---------------------------------|------------------|
| <b>Integral Mounting Feet</b>   | No               |
| <b>Integral Mounting Flange</b> | No               |
| <b>Dual Access</b>              | No               |
| <b>Knockouts</b>                | Yes              |
| <b>Material</b>                 | Galvanized steel |
| <b>Cover Type</b>               | Screw cover      |
| <b>Padlockable</b>              | No               |
| <b>Keylocking</b>               | No               |

## Agency Approvals

|                             |                                        |
|-----------------------------|----------------------------------------|
| <b>UL Listed File #</b>     | E23553                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SC121810G.pdf>  
See store item page for other formats.