

# SC6-1111 Cut Sheet



ProSense signal conditioner, (2) isolated channels, loop powered current input, current output, 35mm DIN rail mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC6-1111>

## Technical Specifications

|                              |                       |
|------------------------------|-----------------------|
| Brand                        | ProSense              |
| Item                         | Signal conditioner    |
| Isolation                    | (2) isolated channels |
| Field Configurable           | No                    |
| Input Current Signal Range   | 0-20 mA loop powered  |
| Input Current Signal Range 2 | 0-20 mA loop powered  |

|                               |                 |
|-------------------------------|-----------------|
| Output Current Signal Range   | 0-20 mA         |
| Output Current Signal Range 2 | 0-20 mA         |
| Housing Material              | Plastic         |
| Mounting                      | 35mm DIN rail   |
| Electrical Connection         | Screw terminals |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | E498965                                |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | None                                   |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |
| Other                | <a href="#">FM Approval Document</a>   |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SC6-1111.pdf>  
See store item page for other formats.