

SC6-2001 Cut Sheet



ProSense signal conditioner, isolated, Input: 1-channel, NAMUR sensor/NPN/dry contact, Output: 2-channel, NPN, 24 VDC operating voltage, 35 mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC6-2001>

Technical Specifications

Brand	ProSense
Item	Signal conditioner
Isolation	Isolated
Field Configurable	Yes
Number Of Input Channels	1
Input	NAMUR sensor/NPN/dry contact
Number Of Output Channels	2
Output	NPN
Operating Voltage	24 VDC
Housing Material	Plastic
Mounting	35 mm DIN rail
Electrical Connection	Screw terminals

Agency Approvals

UL Listed File #	E498965
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SC6-2001.pdf>
See store item page for other formats.